



FreeZone 4.5 Liter -105C Benchtop Freeze Dryers

FreeZone 4.5 Liter Benchtop Freeze Dryers are designed for lyophilizing light to moderate sample loads. The compact design is ideal for labs with limited floor space.

The upright stainless steel collector coil holds 4.5 liters of ice before defrosting. Two 1/2 hp HCFC/CFC-free refrigeration systems cool the collector to -105° C (-157° F) at 60 Hz or -102° C (-152° F) at 50 Hz, suitable for low eutectic point samples including acetonitrile and dilute methanol and ethanol.

Lyo-Works™ OS provides a real time display of collector temperature, vacuum level and optional End-Zone™ end point detection system, shown on a 5" full color, capacitive touch screen. Models with PTFE-coated collectors that can withstand corrosive compounds are available.

- [Stay Connected](#)
- [View Real-Time Sample Data](#)
- [Get Consistent, High Quality Results](#)
- [Make Challenging Samples Easy](#)

Архангельск (8182)63-90-72
Астана (7172)727-132
Астрахань (8512)99-46-04
Барнаул (3852)73-04-60
Белгород (4722)40-23-64
Брянск (4832)59-03-52
Владивосток (423)249-28-31
Волгоград (844)278-03-48
Вологда (8172)26-41-59
Воронеж (473)204-51-73
Екатеринбург (343)384-55-89
Иваново (4932)77-34-06

Ижевск (3412)26-03-58
Иркутск (395)279-98-46
Казань (843)206-01-48
Калининград (4012)72-03-81
Калуга (4842)92-23-67
Кемерово (3842)65-04-62
Киров (8332)68-02-04
Краснодар (861)203-40-90
Красноярск (391)204-63-61
Курск (4712)77-13-04
Липецк (4742)52-20-81

Магнитогорск (3519)55-03-13
Москва (495)268-04-70
Мурманск (8152)59-64-93
Набережные Челны (8552)20-53-41
Нижний Новгород (831)429-08-12
Новокузнецк (3843)20-46-81
Новосибирск (383)227-86-73
Омск (3812)21-46-40
Орел (4862)44-53-42
Оренбург (3532)37-68-04
Пенза (8412)22-31-16

Пермь (342)205-81-47
Ростов-на-Дону (863)308-18-15
Рязань (4912)46-61-64
Самара (846)206-03-16
Санкт-Петербург (812)309-46-40
Саратов (845)249-38-78
Севастополь (8692)22-31-93
Симферополь (3652)67-13-56
Смоленск (4812)29-41-54
Сочи (862)225-72-31
Ставрополь (8652)20-65-13

Сургут (3462)77-98-35
Тверь (4822)63-31-35
Томск (3822)98-41-53
Тула (4872)74-02-29
Тюмень (3452)66-21-18
Ульяновск (8422)24-23-59
Уфа (347)229-48-12
Хабаровск (4212)92-98-04
Челябинск (351)202-03-61
Череповец (8202)49-02-64
Ярославль (4852)69-52-93

Киргизия (996)312-96-26-47

Россия (495)268-04-70

Казахстан (772)734-952-31

<https://labconco.nt-rt.ru/> || bon@nt-rt.ru

Remote notification, data collection, and optional End-Zone™ end point detection with Lyo-Works™ OS on freeze dryer. Suitable for lyophilizing low eutectic point samples including dilute methanol and ethanol.

Additional Features & Specifications

Features (All Models)

- Upright stainless steel collector coil capable of holding 4.5L of ice before defrosting. Stainless steel collector lid, 3/4" thick, has neoprene gasket and 3" diameter port for connection of drying accessories (sold separately).
- Compact benchtop design with a small footprint.
- Brushed stainless steel and glacier white, powder-coated steel exterior with blue accents.
- Full color, 5" capacitive touch screen with Lyo-Works™ OS:
 - Real time display of collector temperature, vacuum level, and optional End-Zone™ end point detection system.
 - Start-up mode for collector cool-down and vacuum pull-down (automatic or manual).
 - Operating mode (standby or run).
 - Vacuum set point, alerts, diagnostic tests, user manual, defrost control, and optional drying accessory

- Data logging stores and displays data in table or chart format, and may be exported via USB or Ethernet.
- Settings include language (English, Spanish, French, German, or Italian), time, time zone, temperature (° C or ° F), and vacuum (mBar, Torr, or Pa).
- Alerts are programmable to send via Ethernet connection to user-entered email addresses.
- Display settings include brightness, touch sounds (on/off), and screen time out in minutes (on/off).
- Maintenance alert settings include vacuum pump oil change, refrigeration cleaning, total operating hours and line voltage offset.
- Level-specific security lock-out prevents changes to programs and other system parameters.
- Hot gas defrost with auto shut off at +60° C (+140° F).
- On/standby switch.
- Moisture sensor that prevents refrigeration or vacuum start-up when moisture is detected in the drain line.
- Vacuum control valve that maintains vacuum level set point.
- Vacuum break valve that bleeds air into the system when power to the freeze dryer or vacuum pump is shut off. If a power outage less than approximately 5 minutes occurs, the freeze dryer will restart and the refrigeration and vacuum system will resume operation once power is restored. If the power failure is more than approximately 5 minutes and the collector warms above safe limits, the freeze dryer will not automatically restart.
- Side-mounted USB port and rear-mounted Ethernet connection.
- Side-mounted, quick-disconnect drain hose fitting and lanyard with hose connector. 1/8", 1/4" ID silicone tubing and clamp included.
- Rear-mounted electrical receptacle for vacuum pump connection.

- 3/4" OD vacuum connection, 50" of 3/4" ID vacuum hose and two clamps.

Options Include

- PTFE-coated collector coil and chamber for processing involving corrosive compounds.
- Region-specific electrical plug configurations.

Required Accessories (Not Included)

- Vacuum pump with a displacement of at least 98 L/min, 0.002 mBar ultimate pressure and fitting suitable for 3/4" ID vacuum hose.
- Small Tray Dryer or other drying accessory.
- Freeze dry glassware if not bulk freeze drying.

[FreeZone 4.5 Liter -105C Benchtop Freeze Dryer](#)



Catalog # 720401000

Region: U.S. and Canada
Collector Temperature: -105° C, -157° F
Ice Holding Capacity: 4.5L
Plug Type: North America, 115V
Style: Benchtop

[FreeZone 4.5 Liter -105C Benchtop Freeze Dryer](#)



Catalog # 720401010

Region: U.S. and Canada, International
Collector Temperature: -105° C, -157° F
Ice Holding Capacity: 4.5L
Plug Type: North America, 230V
Style: Benchtop

[FreeZone 4.5 Liter -105C Benchtop Freeze Dryer](#)



Catalog # 720401015

Region: International

[FreeZone 4.5 Liter -105C Benchtop Freeze Dryer](#)



Catalog # 720401030

Region: International

Collector Temperature: -105° C,
-157° F
Ice Holding Capacity: 4.5L
Plug Type: Saudi Arabia
Style: Benchtop

[FreeZone 4.5 Liter -105C
Benchtop Freeze Dryer](#)



Catalog # 720401040

Region: International
Collector Temperature: -105° C,
-157° F
Ice Holding Capacity: 4.5L
Plug Type: China/Australia
Style: Benchtop

[FreeZone 4.5 Liter -105C
Benchtop Freeze Dryer](#)



Catalog # 720401070

Region: International
Collector Temperature: -105° C,
-157° F
Ice Holding Capacity: 4.5L
Plug Type: India
Style: Benchtop

[FreeZone 4.5 Liter -105C
Benchtop Freeze Dryer](#)



Catalog # 720402010

Region: U.S. and Canada,
International
Collector Temperature: -105° C,
-157° F
Ice Holding Capacity: 4.5L
Options Included: Corrosion-
Resistant Collector

Collector Temperature: -105° C,
-157° F
Ice Holding Capacity: 4.5L
Plug Type: Schuko
Style: Benchtop

[FreeZone 4.5 Liter -105C
Benchtop Freeze Dryer](#)



Catalog # 720401050

Region: International
Collector Temperature: -105° C,
-157° F
Ice Holding Capacity: 4.5L
Plug Type: British (UK)
Style: Benchtop

[FreeZone 4.5 Liter -105C
Benchtop Freeze Dryer](#)



Catalog # 720402000

Region: U.S. and Canada
Collector Temperature: -105° C,
-157° F
Ice Holding Capacity: 4.5L
Options Included: Corrosion-
Resistant Collector
Plug Type: North America, 115V
Style: Benchtop

[FreeZone 4.5 Liter -105C
Benchtop Freeze Dryer](#)



Catalog # 720402015

Region: International
Collector Temperature: -105° C,
-157° F
Ice Holding Capacity: 4.5L
Options Included: Corrosion-
Resistant Collector
Plug Type: Saudi Arabia

FreeZone 4.5 Liter -105C

Benchtop Freeze Dryer



Catalog # 720402030

Region: International

Collector Temperature: -105° C,
-157° F

Ice Holding Capacity: 4.5L

Options Included: Corrosion-
Resistant Collector

Plug Type: Schuko

Style: Benchtop

FreeZone 4.5 Liter -105C

Benchtop Freeze Dryer



Catalog # 720402050

Region: International

Collector Temperature: -105° C,
-157° F

Ice Holding Capacity: 4.5L

Options Included: Corrosion-
Resistant Collector

Plug Type: British (UK)

Style: Benchtop

FreeZone 4.5 Liter -105C

Benchtop Freeze Dryer



Catalog # 720402040

Region: International

Collector Temperature: -105° C,
-157° F

Ice Holding Capacity: 4.5L

Options Included: Corrosion-
Resistant Collector

Plug Type: China/Australia

Style: Benchtop

FreeZone 4.5 Liter -105C

Benchtop Freeze Dryer



Catalog # 720402070

Region: International

Collector Temperature: -105° C,
-157° F

Ice Holding Capacity: 4.5L

Options Included: Corrosion-
Resistant Collector

Plug Type: India

Style: Benchtop

Архангельск (8182)63-90-72
Астана (7172)727-132
Астрахань (8512)99-46-04
Барнаул (3852)73-04-60
Белгород (4722)40-23-64
Брянск (4832)59-03-52
Владивосток (423)249-28-31
Волгоград (844)278-03-48
Вологда (8172)26-41-59
Воронеж (473)204-51-73
Екатеринбург (343)384-55-89
Иваново (4932)77-34-06

Ижевск (3412)26-03-58
Иркутск (395)279-98-46
Казань (843)206-01-48
Калининград (4012)72-03-81
Калуга (4842)92-23-67
Кемерово (3842)65-04-62
Киров (8332)68-02-04
Краснодар (861)203-40-90
Красноярск (391)204-63-61
Курск (4712)77-13-04
Липецк (4742)52-20-81

Киргизия (996)312-96-26-47

Магнитогорск (3519)55-03-13
Москва (495)268-04-70
Мурманск (8152)59-64-93
Набережные Челны (8552)20-53-41
Нижний Новгород (831)429-08-12
Новокузнецк (3843)20-46-81
Новосибирск (383)227-86-73
Омск (3812)21-46-40
Орел (4862)44-53-42
Оренбург (3532)37-68-04
Пенза (8412)22-31-16

Россия (495)268-04-70

Пермь (342)205-81-47
Ростов-на-Дону (863)308-18-15
Рязань (4912)46-61-64
Самара (846)206-03-16
Санкт-Петербург (812)309-46-40
Саратов (845)249-38-78
Севастополь (8692)22-31-93
Симферополь (3652)67-13-56
Смоленск (4812)29-41-54
Сочи (862)225-72-31
Ставрополь (8652)20-65-13

Казахстан (772)734-952-31

Сургут (3462)77-98-35
Тверь (4822)63-31-35
Томск (3822)98-41-53
Тула (4872)74-02-29
Тюмень (3452)66-21-18
Ульяновск (8422)24-23-59
Уфа (347)229-48-12
Хабаровск (4212)92-98-04
Челябинск (351)202-03-61
Череповец (8202)49-02-64
Ярославль (4852)69-52-93

<https://labconco.nt-rt.ru/> || bon@nt-rt.ru